

# SPECTREM® SIMPLE SEAL SEALANT USE GUIDE

		SIMPLE SEAL WIDTH IN INCHES (MILLIMETERS)‡											
Substrate <i>(Surface Condition)</i>	Sealant*	1" <i>(25 mm)</i>	2" <i>(50.8 mm)</i>	3" <i>(76 mm)</i>	4" <i>(101.6 mm)</i>	5" <i>(127 mm)</i>	6" <i>(152 mm)</i>	7" <i>(177.8 mm)</i>	8" <i>(203 mm)</i>	9" <i>(228.6 mm)</i>	10" <i>(254 mm)</i>	11" <i>(279.4 mm)</i>	12" <i>(304.8 mm)</i>
<b>Smooth</b>	Bead size <i>two required**</i>	1/8" <i>(3.2 mm)</i>	1/8" <i>(3.2 mm)</i>	1/8 - 3/16" <i>(3.2 - 4.8 mm)</i>	1/8 - 3/16" <i>(3.2 - 4.8 mm)</i>	3/16 - 1/4" <i>(4.8 - 6.4 mm)</i>	3/16 - 1/4" <i>(4.8 - 6.4 mm)</i>	3/16 - 1/4" <i>(4.8 - 6.4 mm)</i>	3/16 - 1/4" <i>(4.8 - 6.4 mm)</i>	3/16 - 1/4" <i>(4.8 - 6.4 mm)</i>	1/4 - 5/16" <i>(6.4 - 7.9 mm)</i>	1/4 - 5/16" <i>(6.4 - 7.9 mm)</i>	1/4 - 5/16" <i>(6.4 - 7.9 mm)</i>
Aluminum, Metal, Glass	10.1 oz tubes/100'	1.5	1.5	1.5 - 3.5	1.5 - 3.5	3.5 - 6.5	3.5 - 6.5	3.5 - 6.5	3.5 - 6.5	3.5 - 6.5	6.5 - 10	6.5 - 10	6.5 - 10
<b>Medium</b>	Bead size <i>two required**</i>	1/8" <i>(3.2 mm)</i>	1/8 - 3/16" <i>(3.2 - 4.8 mm)</i>	1/8 - 3/16" <i>(3.2 - 4.8 mm)</i>	3/16 - 1/4" <i>(4.8 - 6.4 mm)</i>	3/16 - 1/4" <i>(4.8 - 6.4 mm)</i>	3/16 - 1/4" <i>(4.8 - 6.4 mm)</i>	3/16 - 1/4" <i>(4.8 - 6.4 mm)</i>	1/4 - 5/16" <i>(6.4 - 7.9 mm)</i>	1/4 - 5/16" <i>(6.4 - 7.9 mm)</i>	1/4 - 5/16" <i>(6.4 - 7.9 mm)</i>	5/16 - 3/8" <i>(7.9 - 9.5 mm)</i>	5/16 - 3/8" <i>(7.9 - 9.5 mm)</i>
Brick, EIFS, Concrete, Natural Stone	10.1 oz tubes/100'	1.5	1.5 - 3.5	1.5 - 3.5	3.5 - 6.5	3.5 - 6.5	3.5 - 6.5	3.5 - 6.5	6.5 - 10	6.5 - 10	6.5 - 10	10 - 14.5	10 - 14.5
<b>Rough / Coarse</b>	Bead size <i>two required**</i>	1/8 - 3/16" <i>(3.2 - 4.8 mm)</i>	1/8 - 3/16" <i>(3.2 - 4.8 mm)</i>	3/16 - 1/4" <i>(4.8 - 6.4 mm)</i>	3/16 - 1/4" <i>(4.8 - 6.4 mm)</i>	3/16 - 1/4" <i>(4.8 - 6.4 mm)</i>	1/4 - 5/16" <i>(6.4 - 7.9 mm)</i>	1/4 - 5/16" <i>(6.4 - 7.9 mm)</i>	1/4 - 5/16" <i>(6.4 - 7.9 mm)</i>	1/4 - 5/16" <i>(6.4 - 7.9 mm)</i>	5/16 - 3/8" <i>(7.9 - 9.5 mm)</i>	5/16 - 3/8" <i>(7.9 - 9.5 mm)</i>	5/16 - 3/8" <i>(7.9 - 9.5 mm)</i>
Stucco, EIFS	10.1 oz tubes/100'	1.5 - 3.5	1.5 - 3.5	3.5 - 6.5	3.5 - 6.5	3.5 - 6.5	6.5 - 10	6.5 - 10	6.5 - 10	6.5 - 10	10 - 14.5	10 - 14.5	10 - 14.5

**Notes:** \*Amount of sealant required further depends on the width of the sealant/bond area desired or needed.

\*\*Sealant bead(s) must be applied to substrate on each side of joint to be sealed.

‡Simple Seal is available in 100' (30.4 M) long rolls for material up to 9" (228.6 mm) in width and in 50' (15.2 M) rolls for wider material.

