



ExoAir 220/230

ExoAir TWF, recessed
 1/2" from exterior

Metal drip edge

Spectrem 1 sealant

Paraterm Bar with
 Dymonic 100 or
 Vulkem 116
 Note: Vulkem 116
 must be fully cured
 prior to installing
 ExoAir TWF

TREMDrain

Paraseal

Dymonic 100 or
 ExoAir Termination
 Mastic

ExoAir TWF with
 ExoAir Primer

4" Min.

4" Min.

Dymonic 100,
 Dymeric 240FC or
 Tremflex 834

Paraterm Bar with
 Vulkem 116 (fully
 cured) or
 Dymonic 100

ExoAir TWF

ExoAir Primer

TREMDrain

Paraseal

Note: Paraseal products require a minimum 24 psf compaction/ confinement in order to function as designed

This detail is intended for conceptual purposes only. Detail must be reviewed by a project/design professional. See www.tremcosealants.com for the most up-to-date product information.

Rev	Date	Description	By
-	-	-	-